

# ST20-S

## Semi Trash Pump

ST20-S 2.0"

Model 6919-1 (49ST/Canada)  
UPC: 696471069198

1 of 2



### FEATURES

- Powerful Generac Pump - Can pump up to 158 gallons per minute
- Extended run-time fuel tank with fuel gauge
- Color coded suction and discharge ports to ensure the correct hose connections
- Durable design - Silicon Carbide Seal, Ductile Iron Volute and Impeller
- Powerful Generac G-Force 169cc OHC engine with low oil alert provides longer engine life
- EASY PRIME™ Funnel design for quick and easy priming

## Specifications

Engine Type	4 cycle/OHC
Engine Displacement (cc)	169
Start Type	Recoil Pull Start
Low Oil Shutdown Method	Low Level
Recommended Oil	10W-30 / SAE30
Fuel Capacity (gal/l)	3/11.4
Max Run Time	5.0 hrs
Flow gpm/lpm	158/598
Max Total Head (ft/m)	108/32.9
Max Suction Lift (ft/m)	26/7.9
Mechanical Seal Type	Silicon Carbide
Solid Handling (in)	0.33
Suction Port (NPT)	2.0
Discharge Port (NPT)	2.0
Pump Housing	Aluminum
Impeller	Ductile Cast Iron
Volute	Ductile Cast Iron

Hose Kit Included	N/A
Discharge Hose Length (ft/m)	N/A
Suction Hose Length (ft/m)	N/A
Hose Connections	N/A
Strainer	N/A
Wheel Kit	N/A
Country of Origin	China
Warranty	3 Year Limited
Manual Part #	0K9077
Length (L) (in/mm)	23.1/587
Width (W) (in/mm)	18.1/460
Height (H) (in/mm)	19.8/502
Unit Weight (lbs/kg)	65.3/29.6
Carton Length (in/mm)	23.8/604
Carton Width (in/mm)	18.7/475
Carton Height (in/mm)	20.6/524
Shipping Weight (lbs/kg)	72.5/32.9

